

Lok-it! HTI 1500 W/60/P50

Lok-it! | HTI Short Arc Metal Halide lamps were designed as intense light sources primarily for moving head fixtures in the Entertainment marketplace.



Areas of application

- Concert lighting
- Club & Disco
- Stage and theatre
- Studio, TV and film
- Architecture & Architainment

Product family benefits

- Higher luminous efficacy than conventional HID lamps provides higher fixture efficiency
- Rapid relamping with bayonet lock

Product family features

- Compact design and short arc gap for use in smaller and brighter fixtures
- Fast lamp replacement with one touch thanks to rotating lock
- Robust design with eXtreme Seal (XS) technology, allowing up to 450°C at the pinch seal
- Consistent lumen output over the life of the lamp
- Ceramic base allows high voltage up to 35 kV





Product datasheet

Technical data

Electrical data


| Nominal wattage | 1500.00 W |
|-----------------|---------------------|
| Nominal voltage | 100 V |
| Lamp voltage | 100 V ¹⁾ |
| Nominal current | 15 A |
| Lamp current | 15.0 A |

^{1) ±10} V

Photometrical data

| Nominal luminous flux | 130000 lm | |
|--------------------------|-----------|--|
| Color temperature | 6000 K | |
| Color rendering index Ra | >85 | |

Dimensions & weight



| Diameter | 29.0 mm |
|---------------------------|----------|
| Length | 128.0 mm |
| Light center length (LCL) | 65.0 mm |
| Electrode gap cold | 6.1 mm |

Lifespan

| Lifespan | 750 h |
|----------|-------|
| | |

Environmental information

| Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACh) | | | |
|---|-------------------------------|--|--|
| Date of Declaration | 05-03-2024 | | |
| Primary Article Identifier | 4008321553416 4052899561823 | | |

Product datasheet

| Candidate List Substance 1 | No declarable substances contained | |
|----------------------------------|------------------------------------|--|
| Declaration No. in SCIP database | In work | |

Product datasheet

Safety advice

Because of their high luminance, UV radiation and high internal pressure during operation, Lok-it! lamps may only be operated in enclosed lamp casings specially constructed for the purpose. Appropriate filters must ensure that UV radiation is reduced to an acceptable level. Mercury is released if the lamp breaks. Special safety precautions must be taken. Information on safety and handling is available on request or can be found in the leaflet included with the lamp or in the operating instructions.

Logistical Data

| Product code | Product description | Packaging unit (Pieces/Unit) | Dimensions (length x width x height) | Volume | Gross weight |
|---------------|------------------------------|---------------------------------|--------------------------------------|----------------------|--------------|
| 4008321553416 | Lok-it! HTI 1500 W/60/P50 | Shipping carton box 1 | 115 mm x 82 mm x 305 mm | 2.88 dm ³ | 249.00 g |
| 4062172308199 | Lok-it! HTI 1500 W/60/P50 | Shipping carton box 10 | - x - x - | | |

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.