

# QBM D4i LS/PD HB R

# Qualified Bluetooth mesh D4i Module | Light management systems



#### Product family features

- With/without Daylight and Occupancy Sensor DEXAL Module
- Qualified Bluetooth mesh enabled by Silvair
- Control of DEXAL drivers or DALI drivers with additional DALI bus power supply
- Intended for installation into a standard 1/2" knockout
- Works with OSRAM Hubsense
- Works with OSRAM DEXAL

#### Product family benefits

- Design freedom due to compact size
- Easy to integrate in luminaire
- Minimize internal wiring in combination with DEXAL drivers
- Secured product communication granted by ioXT and PSA Certificates

#### Areas of application


- Open offices
- Individual offices
- Conference rooms
- Classrooms
- Storage and break areas
- Stairways
- Toilets


#### Technical data

#### **Electrical data**

Input voltage DC	1222.5 V		
Peak input current	30 mA		
Average input current	10 mA		
Radio frequency	2.4 GHz		
Maximum TX power	+4 dBm		
Wireless protocol	Qualified Bluetooth mesh enabled by Silvair		
Wireless range	12 m line of sight		
System wattage	030 W		
Standby power	< 150 mW		
Screw thread length	25 mm		
Required DALI current (typical)	10 mA		
Peak DALI current	30 mA		
Maximum start-up time (DALI)	-		

### **Dimensions & weight**





Length	435 mm		
Diameter	370 mm		
Mounting hole diameter	22.223.2 mm		
Product weight	1820 g		
Wire preparation length, input side	79 mm		
Cable cross-section, output side	-		
Cable cross-section, input side	0.250.75 mm <sup>2</sup>		
Maximum allowed cable length	10		
Screw thread length	25 mm		

## Temperatures & operating conditions

Temperature range in operation at Tc point	-
Ambient temperature range	-20+50 °C
Permitted rel. humidity during operation	090 %
Temperature range at storage	070 °C
Permitted relative humidity at storage	095 %
Maximum temperature at tc test point	60 °C

### Lifespan

Lifespan	50000 h
----------	---------

### **Capabilities**

Control output	D4i				
Number of connected drivers	4				
Dimmable	Yes				
Type of sensor	Daylight / PIR				
Operating range, light sensor	<1000 lx				
Detection angle	90 °				
Maximum installation height	-				
Compatibility	Works with OSRAM HubSense / Works with OSRAM DEXAL				
Status Indicator	Blue: network Status / Red: Motion detected				
Reset	Magnetic <sup>1)</sup>				
Number of control outputs	-				
Dimming interface	D4i				
Type of installation	Luminaire integration				
Control interface	qualified Bluetooth mesh				
Detection angle (Light sensor)	+/- 15°				
Detection angle (PIR)	+/-60°				

<sup>1)</sup> by magnet

### **Certificates & standards**

Approval marks – approval	CE / ioXT / PSA		
Type of protection	IP65		


### Logistical data

Commodity sada	90314990000
Commodity code	90314990000

#### **Environmental information**

Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACh)


Date of Declaration	05-12-2023		
Primary Article Identifier	4052899627178		
Candidate List Substance 1	Lead		
CAS No. of substance 1	7439-92-1		
Safe Use Instruction	The identification of the Candidate List substance is sufficient to allow safe use of the article.		
Declaration No. in SCIP database	a300203b-99f6-421f-995e-77119a1adad2		




QBM D4I LS PD HB R Detection Pattern 4




QBM D4I LS PD HB R Detection Pattern 3




QBM D4I LS PD HB R Detection Pattern 2




QBM D4I LS PD HB R Detection Pattern 1





QBM D4I LS PD HB R Detection\_Pattern

210722 RA231HA8 detection



210722 RA231HA8 Detection Pattern

#### Additional product information

- By integrating the device into a casing the wireless range could be affected, in particular by metal surfaces. Therefore, the wireless range needs to be verified after integration.
- The device could be reset to factory default by placing a strong Neodym magnet (e.g. N35, d=6.35 mm x h=1.59 mm) near the corner of the bezel for 5 seconds.
- The status LED of the device indicates following Network status. Fast blinking (Blue): Not connected to a network, Slow blinking (Blue); Connected to a network, Blink twice (Blue): Mesh package received, Long blink (Blue) Factory reset, Blink one (Red): Motion detected
- The device has passed successfully the SILVAIR Testing process.
- The device can be put into operation using the OSRAM HubSense Commissioning Tool (https://platform.hubsense.eu), subject to prior acceptance of the Terms of Use and the Privacy Policy.
- OSRAM may terminate or suspend the use of the HubSense Commissioning Tool at any time and for any or no reason in its sole discretion, even if access and use is continued to be allowed to others.
- The device complies with Bluetooth mesh Standard v1.0. It can also be used in 3rd party Bluetooth mesh network, that complies with this standard and that supports the mesh models of this device, and with certain 3rd party commissioning tools, that support the mesh models of this device. In order to ensure correct interoperability a verification with the 3rd party network components and the 3rd party commissioning tool is necessary in advance. Please contact OSRAM (support@hubsense.eu) to receive the actual list of supported models for this device.
- OSRAM shall have no liability for any 3rd party commissioning tool and does not make any representations, express or implied, about the availability and/or performance of such commissioning tool.
- OSRAM shall have no liability for and does not make any representations, express or implied, about the connectivity of OSRAM QBM products with any other products, that have passed the SILVAIR Testing process.

#### Download Data

	File
大	User instruction QBM D4I LS PD HB R
大	User instruction QBM D4I LS PD R Qualified Bluetooth Mesh Presence Daylight Sensor LENS SHIELDS

#### Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4052899627178	QBM D4i LS/PD HB R	Shipping carton box 50	330 mm x 287 mm x 195 mm	18.47 dm³	1530.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.